

## TECHNICAL SPECIFICATIONS

Material: Injection moulded flame retardant ABS  
Diameter: 92mm int.  
Height: 140mm



- accommodates mousetrap and butterfly fittings
- accepts most generic brands of electronic transformers
- suitable for 12v & 240v halogen, fluorescent, LED, and some R80 downlights.



HEAT REFLECTOR for use with 12v and 240v halogen fittings.



# APE-SC

Pat. Pending 2009905788

# APE-SC


Pat. Pending 2009905788

APE Slab Canisters accommodate fittings with both 'mousetrap' and 'butterfly' clips, accept most generic brands of electronic transformers and are suitable for 12v & 240v halogen (with optional heatshield), fluorescent, LED, and some R80 downlights.

## INSTALLATION INSTRUCTIONS

### PRIOR TO POUR:


Install conduit, fix canister to formwork using mounting tabs, tie down conduit, apply PVC glue.



### AFTER POUR:

1. Connect transformer and insert into housing.

2. Connect globe and fitting. If installing halogen fittings use of an aluminium-backed lamp is suggested. A heat reflector is included with the APE Slab Canister.



3. Insert fitting. Units with butterfly clips simply slide into place. Units with mousetrap clips can be secured to the internal locator bosses.

Note: it is the installers responsibility to ensure that lighting equipment used in conjunction with APE Manufacturing Slab Canisters meets appropriate standards, is correctly installed, and is compatible with APE SCs.

## APE MANUFACTURING

Please contact your nearest electrical retailer

website: [www.apemanufacturing.com.au](http://www.apemanufacturing.com.au)

# APE SLAB CANISTER

Patent Pending 2009905788

ONE-PIECE  
SAVES TIME  
SAVES MONEY



BUTTERFLY  
MOUSETRAP  
12v, 240v HALOGEN  
FLUORO, LED & R80



